


CONNETTORE TIPO A (CON MOLLA DI RITEGNO ESTERNA)
CONNECTOR TYPE B (WITH INTERNAL SPRING)

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



MARRONE (BROWN)	282729-6	E1	3	\\\\\\\\\\\\\\	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)		
BLU (BLUE)	282729-5		2	NATURALE (NATURAL)	GOMMA SILICONE (SILICONE RUBBER)	GUARNIZIONE (SEALING)		
VERDE (GREEN)	282729-4		1	\\\\\\\\\\\\\\	PA 6.6	BLOCCETTO (HOUSING)		
NATURALE (NATUR)	282729-3							
GRIGIO (GREY)	282729-2							
NERO (BLACK)	282729-1							
COLORE (COLOR)	NUMERO (PART. N°)	ASSY REV.	N° (ITEM)	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)		
			CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		
			THIS DRAWING IS UNPUBLISHED			RELEASE FOR PUBLICATION 19		
			© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING					
			TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)			DIAM. ISOLANTE (INS. DIA. RANGE) 1.5-3.0 mm (RED. INS. CABLE)	RANGO FILO (WIRE RANGE) 0.5-2.5 mm²	SCALA (SCALE) ---
E1	REVISED PER ECO-16-003585	MP	15MAR 2016	± 0.3			 TE Connectivity	
E	ECR-14-003472	MP	24MAR 2014	ANGOLI (ANGLES) ± 2°				
D	REVISED FOR ET00-0385-99	M.P.	2-4 01	DIS. 19 MAY 95 (DR.) M. PALMA			DESCRIZIONE (DESCRIPTION) 3 POS. SPLASH PROOF CONN. ASS'Y with SECONDARY LOCK	
C	RELEASED FOR PRODUCTION -6, WITH EC ET00-0222-98	R.M.		CONT. 19 MAY 95 (CHK) C. TARTARI				
B	REVISED AND IN PRODUCTION EC ET00-0075-96	A.B.	12-2 1996				LOC. SIZE NUMERO (DWG NO) REV. E1	
A	FIRST ISSUE WITH ECN ET00-0217-95	M.P.	15-9 1995					
REV. (REV. LTR.)	REVISIONI (REVISION RECORD)	DIS. (DR)	DATA (DATE)	APP. (APP.)			FOGLIO (SHEET) 1 DI 2	

