

Socket - EM-DUO 120/15/V/H - 5604747

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Rail-mounted dual socket for vertical or horizontal mounting on 35 mm DIN rail per EN 60715. Housing color: ivory. Receptacle style: USA. Connection type: screw.

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	271.2 g
Custom tariff number	85366990
Country of origin	United States

Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

General

Nominal voltage U_N	125 V AC
Nominal current I_N	15 A
For country-specific use in	USA
	Canada
	Japan
	Mexico
	Saudi Arabia
	Taiwan
	Venezuela
Color	ivory
Insulating material	PVC 94 V0
Standards/regulations	UL 508
	CSA 22.2

Connection data

Conductor cross section solid min.	0.2 mm ²
------------------------------------	---------------------

Socket - EM-DUO 120/15/V/H - 5604747

Technical data

Connection data

Conductor cross section solid max.	6 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	4 mm ²
Conductor cross section AWG min.	30
Conductor cross section AWG max.	10
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3

Standards and Regulations

Standards/regulations	UL 508
	CSA 22.2

Classifications

eCl@ss

eCl@ss 4.0	27142305
eCl@ss 4.1	27142305
eCl@ss 5.0	27143412
eCl@ss 5.1	27130801
eCl@ss 6.0	27130803
eCl@ss 7.0	27130803
eCl@ss 8.0	27142305

ETIM

ETIM 3.0	EC001325
ETIM 4.0	EC001663
ETIM 5.0	EC001663

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620