



## FEATURES:

- Provides quick access from a WE 310 Jack to a BNC (Female)
- BNC connector is molded directly to the cable for added pull strength

## MATERIALS:

Connectors: BNC Male

Body: Brass, Tarnish resistant plating

Dielectric: PTFE

Center Contact – Gold Plated Brass

Strain Relief: PVC molded directly to cable and connectors

WE 310: 3 Conductor phone plug, sleeve not connected

Cable Marking: "Pomona 6518-96"

## RATINGS:

Operating Voltage: 300 VRMS

## ORDERING INFORMATION: Model 6518-96

Standard Length = 96" (243 cm)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA