

**Aven Inc.**  
4595 Platt Rd.  
Ann Arbor, MI 48108  
**Phone:** 734.973.0099  
**Email:** [info@aventools.com](mailto:info@aventools.com) • **Web Address:** [www.aventools.com](http://www.aventools.com)

[All Categories](#) > [Hand Tools](#) > [Tweezers and Smart Tweezers](#) > [Ceramic Tweezers](#) > [Item # 18822](#)

### Item # 18822, 8° Angled Ceramic Tip Tweezers w Plastic Body



Zirconia ceramic tips. Contamination free. Temperature resistant to 1500 degree C. Solder and wear resistant. Plastic handles

Bent smooth tips. Tip width: 2mm

[larger image](#)

[Features](#) · [Specifications](#)

#### Features

- Extremely smooth surface and very low coefficient of friction.
- Low thermal conductivity and high thermal shock resistance.
- Excellent electric loss at very high frequency range (VHF, UHF, and SHF).
- Will not cause electromagnetic induction or eddy current loss in high frequency.
- 100% non magnetic, non rusting and non static.
- Highly resistant to all strong acids except hydrofluoric.
- Free from all metallic contamination.
- Solder will not adhere to surface.
- Six times harder than stainless steel.
- Two times harder than carbon steel.
- Will hold tip geometry better than metal.
- Can be subject to microwaves for sterilization.
- Thermal insulators well suited for soldering.
- Resistant to 1500°C

#### Specifications

|                       |                       |
|-----------------------|-----------------------|
| Tip                   | Bent smooth, 2mm wide |
| Length                | 4 3/4 in<br>120 mm    |
| Resistant Temperature | 1500 °C               |

[Print](#) [Back](#)