

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050030](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Super-Safeway Rubber Hand Lamp 75W with LOVOLT In-line Transformer Screw Release Reflector Guard 14/2 SOOW Cord Type, 7.62m (25.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130105](#)
NEMA Configuration NEMA 5-15
Outlet None
Overview [Specialty Lighting](#)
Product Name Super-Safeway
Type Hand Lamps, Specialty Light
UPC 78678862501

Physical

Cord Length - Primary 3.04m (10.0')
Cord Length - Secondary 7.62m (25.0')
Depth 101.60mm (4.000")
Duty Industrial
Guard Included Yes
Guard Type Reflector, Screw Release
Height 374.65mm (14.750")
Length N/A
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Cord Type - Secondary 14/2 SOOW
Lamp Type A21
Lamp Wattage - Maximum 75W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ
Voltage (Secondary) - Maximum 12V AC

Material Info

Engineering Number 1601-12A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130105](#) Series