

Specification Sheet

Part Number: 170-03095



Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required.

Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.

Braided Sleeving, Expandable, Flame Retardant, 1.5" Dia, PET, Black, 200 ft/bulk reel

Article Number	170-03095
----------------	-----------

Type	BSPFR1120B
------	------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification. This fire extinguishing braided sleeving is ideal for electronic and high tech applications because of its lightweight and durable qualities.
---------------------	--

Short Description	Braided Sleeving, Expandable, Flame Retardant, 1.5" Dia, PET, Black, 200 ft/bulk reel
-------------------	---

Global Part Name	BSPFR1120B-PET-BK
Length L (Imperial)	200.0
Length L (Metric)	61.0
Bundle Diameter Min (Imperial)	1
Bundle Diameter Min (Metric)	25.4
Bundle Diameter Max (Imperial)	2.13
Bundle Diameter Max (Metric)	54.0
Diameter D (Imperial)	1.5
Diameter D (Metric)	38.1
Nominal Diameter (Imperial)	1.5
Nominal Diameter (Metric)	38.1
Material	Polyester (PET)
Material Shortcut	PET
Flammability	FMVSS 302 FAR 25 Mil-202 UL 224 VW-1
Halogen Free	Yes

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 94 VW-1
UL Recognized (US)	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	60.96
Customs Number	5808100000

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com