


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

|                                |                                                                                                                                                |
|--------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Material                       | High Conductivity Seamless Copper Tube                                                                                                         |
| Plating                        | Electro-Tin                                                                                                                                    |
| UL Listed Wire Connector       | Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts. |
| UL Temperature Rating          | 90° C                                                                                                                                          |
| C.S.A Certified Wire Connector | Yes                                                                                                                                            |

|                                                 | From                                                                             | To                                                                               |
|-------------------------------------------------|----------------------------------------------------------------------------------|----------------------------------------------------------------------------------|
| Wire Sizes                                      | 4/0 AWG                                                                          | 4-3 AWG STR & 2 AWG SOLID                                                        |
| Wire Types                                      | Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric | Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric |
| Wire Strip Lengths                              | 1-1/16 in.                                                                       | 1-5/16 in.                                                                       |
| Panduit Color Code on Barrels                   | PURPLE                                                                           | GRAY                                                                             |
| Panduit Die Index No. on Barrels                | P54                                                                              | P29                                                                              |
| Alternate Industry Die Index No. ( ) on Barrels | (15)                                                                             | (8)                                                                              |



LISTED Wire Connector



|     |      |      |      |                         |       |                                                     |                                     |
|-----|------|------|------|-------------------------|-------|-----------------------------------------------------|-------------------------------------|
|     |      |      |      |                         |       | <b>PANDUIT CORP. TINLEY PARK, ILLINOIS</b>          |                                     |
|     |      |      |      |                         |       | <b>RSC4/0-4-X</b>                                   |                                     |
|     |      |      |      |                         |       | <b>Copper Reducing Splice With Inspection Holes</b> |                                     |
| 03  | 3/04 | KLFU | KLFU | Wire size TO was: 4 AWG | 11644 | SCALE N/A                                           | DRAWING NO / CAD FILE RSC4_0-4-CUST |
| REV | DATE | BY   | CHK  | DESCRIPTION             | ECN   |                                                     |                                     |