



## EDL Lighting limited

Redbrook Lane, Brereton, Rugeley, Staffordshire WS 15 1QU  
Tel: 01889 582112 Fax: 01889 584012 e mail: sales@edl-lighting.co.uk  
Web: www.edl-lighting.co.uk

### ***Haloflex Luminaire***

The Haloflex range is designed for maximum positioning flexibility in the head movement. The flexible gooseneck arm is either 150mm or 700mm long. A 12/24 volt 20 watt halogen lamp is supplied in either IP 21 or IP 54 version. The product is available with or without a transformer in the base. A range of accessories are available to increase the advantages of this luminaire

Version: HAL-L-IP21-20W-12V-NT

Order Code 00630



Dimensional line drawing  
when available

|                          |                                                 |
|--------------------------|-------------------------------------------------|
| Primary voltage:         | 12v                                             |
| Secondary voltage:       | Not applicable                                  |
| Lamp type:               | Halogen                                         |
| Wattage:                 | 20 watt                                         |
| Lamp base type           |                                                 |
| Switch fitted Yes/No:    | Yes                                             |
| Switch location:         | On Head                                         |
| IP Rating                | IP21                                            |
| Base Type:               | Screw down                                      |
| Fixing:                  | Can be horizontal or vertically mounted         |
| No of arms:              | 1                                               |
| Length of arms           | 700mm flexible                                  |
| Arm Material:            | Covered flexible steel                          |
| Shade size and material: | 70mm diameter moulded plastic                   |
| Shield fitted:           | No (available as accessory)                     |
| Shield material          | Clear acrylic or polycarbonate                  |
| Visor fitted:            | No                                              |
| Articulation movement:   | Flexible                                        |
| Joint type:              | Flexible                                        |
| Trailing cable:          | Yes                                             |
| Plug fitted              | Yes (car type - can be removed for hard wiring) |
| Manufacturing Standard:  | BS EN 60598                                     |
| RHOS compliant           | Not applicable                                  |
| WEE Compliant            | Not applicable                                  |
| Finish & Colour:         | Black                                           |



## EDL Lighting limited

Redbrook Lane, Brereton, Rugeley, Staffordshire WS 15 1QU  
Tel: 01889 582112 Fax: 01889 584012 e mail: sales@edl-lighting.co.uk  
Web: www.edl-lighting.co.uk

The Haloflex range is designed for maximum positioning flexibility in the head movement. The flexible gooseneck arm is either 150mm or 700mm long. A 12/24 volt 20 watt halogen lamp is supplied in either IP 21 or IP 54 version. The product is available with or without a transformer in the base. A range of accessories are available to increase the advantages of this luminaire

Version: HAL-L-IP21-20W-12V-NT

Order Code 00630

### Features

Variety of Input voltages

Choice of arm lengths

20 watt halogen lamp fitted

Screw down base

Switch on head

Protective lens available (optional extra)

Option accessories include wall bracket, magnet, lens cover and clamp

Clamp



Protective Lens



Wall Bracket



Clamp Fitted to Base

Protective Lens Fitted to Head



Wall Bracket Fitted to Base



Magnet



Magnet Fitted to Base

