

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT 15 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

,19

REVISIONS

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14					E EC 0720-0279-93	6-21-93	SSS BB


AMP
WIRE RANGE

2 AWG
STRANDED

METRIOS

DIMENSIONS LISTED IN mm [INCHES]

1. TONGUE MATERIAL THK 1.45±0.08[.057±.003]
FOR 11.89[.468] MAX WIRE INS DIA



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
26.7-42.4mm² [52,500-83,700]
STRANDED

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
1-800-522-6752

FOR APPLICATION
TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY
1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

MS25036-128
CLASS 2

MILITARY P/N & CLASS

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.20(.008)
3 PLC DEC ± .1
ANGLES

MATERIAL
COPPER PER ASTM B-152
NYLON (MIL-M-20693) TYPE 1
COLOR: RED

FINISH
TIN PLATE PER MIL-T-10727

LOOSE PC

324055

PACKAGE TYPE

PART NO

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE, TERMINYL
WIRE SIZE: 2 AWG

SIZE
CAGE CODE
DRAWING NO

B 00779 C=324055

SCALE
NTS SHEET 1 OF 1

AMP 1470-15 REV 3-92
21 JUN 1993 09:38:55

AMPT1122 <U0128A>DEPT1132>AMPT1122>U.CUSTOMINYL

CUSTOMER DRAWING