

General Speaker

■ Features

- Reproduces wide range of frequencies
- Wide variety of applications
- Wide product range

■ Recommended Applications

- CD-radio-cassette recorders, Radios
- Information and communication equipment






■ Specifications

Part No.	Input (W)		(Ω) Imp.	fo (Hz)	(Hz) Frequency Range	S.P.L.* (dB/1 W/ 0.5 m)	(g) Mass	Comments
	Rated	max.						
EAS-4P15SA	0.1	—	8	530	fo - 3k	92.0	25	
EAS-45P30S	0.1	—	8		fo - 3k	93.0	24	
EAS-6P22S	0.5	—	8		Full Range	92.0	75	
EAS-8P36S	0.63	—	25		Full Range	95.0	83	
EAS-4D02CO	1	—	16		Full Range	73.0	12	
EAS-G7D504A2	1.5	—	16		Full Range	90.0	107	
EAS-G9D550B2	1.5	—	16		Full Range	87.0	45	
EAS-G9D541A2	3	—	8		Full Range	88.5	135	
EAS-G12D531E2	3	—	8		Full Range	93.5	180	

EAS4P15SA

Dimensions in mm (not to scale)




EAS4P15SA



EAS45P30S


Dimensions in mm (not to scale)

EAS45P30S




EAS6P22S

Dimensions in mm (not to scale)




EAS8P36S

Dimensions in mm (not to scale)




EAS4D02C0

Dimensions in mm (not to scale)




EASG7D504A2

Dimensions in mm (not to scale)




EASG9D550B2

Dimensions in mm (not to scale)



EASG9D541A2

Dimensions in mm (not to scale)



EASG12D531E2

Dimensions in mm (not to scale)

