

## Protective covers - VC-SD-T2 - 1886731

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOCON protective cover for sleeve housing, with IP50 protection, type 2, max. tightening torque: 1.6 Nm

The figure shows the version VC-SD-T1

### Why buy this product

- Easy mounting
- Contact inserts are protected when not plugged in



### Key Commercial Data

Packing unit	5 STK
GTIN	 4 017918 908423
GTIN	4017918908423

### Technical data

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 80 °C

#### General

Size	VC2
Type	For sleeve housing
Material	PA
Flammability rating according to UL 94	V0
Seal present	no
Assembly instructions	Tightening torque 1.6 Nm
Mounting type	Screw locking

#### Standards and Regulations

## Protective covers - VC-SD-T2 - 1886731


### Technical data

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Drawings

Dimensional drawing



---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>