

Coupler connector - SM-7EP1N8A9L02 - 1607066

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Coupler connector, straight long, Screw locking, M40, number of positions: 4+3+PE, type of contact: Pin, shielded: yes, cable diameter range: 8.5 mm ... 12.5 mm, connection method: Crimp connection




Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 255103
GTIN	4046356255103
Weight per Piece (excluding packing)	298.650 g
Custom tariff number	85366990
Country of origin	Germany

Drawings

Coupler connector - SM-7EP1N8A9L02 - 1607066

Schematic diagram



Connector pin assignment

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700

Coupler connector - SM-7EP1N8A9L02 - 1607066

Classifications

eCl@ss

eCl@ss 7.0	27440312
eCl@ss 8.0	27440312
eCl@ss 9.0	27440312

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC001121
ETIM 6.0	EC002641

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39121419
UNSPSC 19.0	39121419