


HONEYWELL
PART NUMBER

6PA358

FAA-PMA 

REV	DOCUMENT	CHANGED BY	CHECK
6	0017178	KRB 25 NOV 05	RJ



NOTES

- 1 - PARTS FURNISHED UNASSEMBLED IN BULK AS A PACKET
- 2 - LEVER MAY BE ADJUSTED FOR AN INFINITE NUMBER OF POSITIONS THRU 360°
-  3 - DO NOT APPLY MORE THAN 20-25 INCH-POUNDS OF TORQUE WHEN TIGHTENING LOCKING NUT
-  4 - FOR MANUFACTURING DETAILS SEE ASSEMBLY DRAWING 6PA358 FOR FAA-PMA
- 5 - RAW MATERIAL: COMMERCIAL STANDARD

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:

NO PLACE	X	$\pm$	0.040
ONE PLACE	.X	$\pm$	0.030
TWO PLACE	.XX	$\pm$	0.015
THREE PLACE	.XXX	$\pm$	0.005
FOUR PLACE	.XXXX	$\pm$	0.0005
ANGLES		$\pm$	2

THIRD ANGLE PROJECTION



DRAWN	TJO	15JAN90
CHECK	GRT	16JAN90
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell

TITLE

LEVER - ADJUSTABLE

SIZE	TYPE	DRAWING NAME	REV
B	I	6PA358	6
SCALE FULL		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[6PA358](#)