







3.5mm Mono

161-1640-EX

KOBICONN

3.5mm Mono



DIMENSIONS mm (in.)
(except where noted)

SPECIFICATIONS

Dielectric strength:	500V AC for one minute
Contact resistance:	50mΩ max
Insulation resistance:	100MΩ min. at 500V DC
RoHS Compliant by Exemption	

Mating Plugs

17PP047-EX, 171-3200-EX, 171-3201-EX, 171-3302-EX

Date Last Revised: 06-06-07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-300852

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-1640-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-1640-EX](#)