

Tina3 series



Ordering number FA11824
Description FA11824_Tina3-W-XP

Family	Tina3	FWHM	40,8 degrees
Type	Lens	Efficiency	-
LED	XP-E	cd/Im	-
Color	White	Gerber File	Available
Diameter	16.3 mm		
Height	7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		



Ordering number FA11825
Description FA11825_Tina3-WW-XP

Family	Tina3	FWHM	62 degrees
Type	Lens	Efficiency	-
LED	XP-E	cd/Im	-
Color	White	Gerber File	Available
Diameter	16.3 mm		
Height	7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	Ready		



Ordering number FA11826
Description FA11826_Tina3-WWW-XP

Family	Tina3	FWHM	78 degrees
Type	Lens	Efficiency	-
LED	XP-E	cd/Im	-
Color	White	Gerber File	Available
Diameter	16.3 mm		
Height	7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		



Ordering number FA11870
Description FA11870_Tina3-OO-XP

Family	Tina3	FWHM	35+53 degrees
Type	Lens	Efficiency	-
LED	XP-E	cd/Im	-
Color	White	Gerber File	Available
Diameter	16.3 mm		
Height	7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		

Tina3 series



Ordering number FA11905
Description FA11905_Tina3-S-XP

Family	Tina3	FWHM	9,6 degrees
Type	Lens	Efficiency	-
LED	XP-E	cd/lm	-
Color	White	Gerber File	Available
Diameter	16.3 mm		
Height	11.5 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		