

 MATERIALS AND FINISH 284512-3 A
 HOUSING : PA 6.6, UL 94-V0, COLOR GREEN
 TERMINAL : PHOSPHOR BRONZE, PLATING: SEE TABLE.





2. SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS

3 NOT CUMULATIVE TOLERANCE

 PRELIMINARY - NOT FOR PRODUCTION.

5 SPECIAL CODING LOCATED AT POSITION 2.
PART TO BE MATED WITH 2-284506-9.

6 SPECIAL CODING LOCATED AT POSITION 1 AND 2.
PART TO BE MATED WITH 3-284506-0.




RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	$\pm$ -
1 PLC	$\pm$.3
2 PLC	$\pm$.25
3 PLC	$\pm$ -
4 PLC	$\pm$ -
ANGLES	

ANGLES
FINISH

DWN	06FEB2002
5	ZANGLI

E. ZANOLINI	
CHK	06

CHK 06 FEB 2002
F ZANOLI INI

E. ZANOLINI	
APVD	06

D. BIEVENOU

PRODUCT SPEC	
--------------	--

108-20166

APPLICATION SPEC

APPLICATION SPEC
114 20070

114-20079

WEIGHT -

CUSTOMER DRAW



TE Connectivity

NAME	TERMINAL BLOCK, HEADER ASSEMBLY 90 DEGREE, CLOSED ENDS 3.5mm PITCH
------	--

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A 300779C-284512

SCALE		SHEET 05		REV
-------	--	----------	--	-----

SCALE	4 : 1	SHEET		OF		REV	F3
-------	-------	-------	--	----	--	-----	----