


Part No.	(5)Length	Part No.	(5)Length
3603-1	1M	3603-5	5M
3603-2	2M	3603-10	10M
3603-3	3M	3603-15	15M



Specification:

- Connector Type : II SC/PC Multimode
- Cable Type :
2-1 Zipcord cable, $\varnothing 3.0\text{mm}$, 50/125um Multimode,
2-2 Calbe Jacket : Orange color, LSZH material
- Cable Marker
- Shrink Tube
- Length : xM

Performance:

- Insertion Loss : $< 0.5 \text{ dB}$
- Fiber Extention : $-0.05\text{um} < H < +0.05\text{um}$
- Ferrule End-face Radius : $10 < R < 25\text{mm}$
- Apex Offset : $< 50\text{um}$
- Increase in insertion loss after 500 mating : 0.2 dB Max.
- Operation Temperature : $-20^\circ \text{ to } +70^\circ$
- Storage Temperature : $-40^\circ \text{ to } +80^\circ$

RoHS Compliant

	DSGN	CSQ	30.MAY.2007	ITEM NO: 3603
	CHK	Maer	30.MAY.2007	
	UNIT M/M	APPR	Yty	30.MAY.2007
SCALE 1/1	Videk Ltd			
DWG NO: 3603				

Videk Ltd