

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FARGO, MINN.

FED. MFR. CODE 91929

ASSEMBLY- PUSHBUTTON SWITCH



CATALOG LISTING
IPB5-T

(M) IPB5-T
ISSUE 2

IPB5-T

M

DRAWING
NUMBER

3*

ISSUE

6

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO 14422
	L M H
	20 JUL 60
B	CO 19743
	M B F
	6 APR 65
C	CO 37671A
	C J H
	11 NOV 77
D	0018502
	PM
	27 FEB 06



CHECK

DRAWN 22 JUL 60

CHECK

L M H 20 JUL 60

FO-50378



NOTE -

- ① 1 - UNIT INCLUDES CAT. LIST "ISM" TYPE BASIC SWITCH
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - RECOMMENDED FOR MANUAL OPERATION ONLY
- ④ MOUNTING HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE-----1 LB APPROX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
	250 VAC ----- 5 AMP	UNLESS OTHERWISE SPECIFIED
	30 VOLTS DC RATING	DIMENSIONS ARE IN INCHES
	INDUCTIVE ----- SEA LEVEL ----- 3 AMP	TOLERANCES ARE:
	50,000 FT. ----- 2.5 AMP	ONE PLACE (.0) ±.030
	RESISTIVE ----- SEA LEVEL ----- 5 AMP	TWO PLACE (.00) ±.015
	50,000 FT. ----- 5 AMP	THREE PLACE (.000) ±.005
	MAXIMUM INRUSH ----- 24 AMP	ANGLES ±
		WEIGHT