



Jack

16PJ227

KOBI CONN

Jack



Dimensions: In.
(except where noted)

SPECIFICATIONS

Type:	2.5mm inline mono
Breakdown voltage:	500VAC for 1 minute
Insulation resistance:	100MΩ min. @ 500VDC
Contact resistance:	50mΩ max.
Rated life:	5,000VAC for 1 min.
Contact A:	Nickel plated brass
Contact B:	nickel plated phosphor bronze
Cap:	polyethylene
Body:	Polyamide
Terminal:	Nickel plated brass

Date Last Revised: 4-4-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300414

16PJ227

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[16PJ227](#)