

MNX ABS 175/125 HT



Sample photo

Order symbol: ABS 175/125 HT
Product nbr: 6081922
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN:	6418074052346
El. number:	
Finland:	3435232
Denmark:	8212023851
Norway:	

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		180	180	125	Ingress Protection (EN 60529): IP 66/67
inch:		7.1	7.1	4.9	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		Smoked grey			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Polyamide			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Cover screws colour:		Black			
Gasket material:		TPE			
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			Fimko
Continuous:		-40 ... 60 °C			Europe EN 62208: 2003
Short term:		-40 ... 175 °F			Gost R
Continuous:		-40 ... 140 °F			
Accessories:					
MIV 175		Mounting plate (Galvanized steel)			
MIN 15		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
FP A 175/180		Front plate (Aluminium)			
HFP 180		Front plate hinge series (2 pcs)			
FP 22046		Wall fastening lug (4 pcs)			

