




REV.	DATE	DESCRIPTION
A	12/09/03	UPDATE DRAWING FORMAT
B	07/08/07	ADD CABLE DESCRIPTION



RECOMMENDED CABLE
STRIPPING DIM'S.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.						07/08/07
7						CHECKED							
6						ISSUED			PART DESCRIPTION F DIRECT SOLDER PLUG (FOR .085” SEMI RIGID CABLE)				
5						SHEET	1 OF 1						
4									PART NO. 222115				
3	CONTACT PIN	BRASS	BRT. TIN	1									
2	INSULATOR	TEFLON	NATURAL	1					DWG. NO. 222115.DWG				
1	BODY	BRASS	TIN—LEAD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE C:/222/222115.DWG			REV. B	SIZE A	SCALE NA		