



T30L0HSM4

High Temp Cable Tie, 7.8" Long, 30lb Tensile Strength, PA66HS, Black, 1000/pkg

Article Number: 111-03341

Part Number: T30L0HSM4

Type: T30L

Base Data

Part No.	T30L0HSM4
Type	T30L
Color	Black (BK)
Features	• Heat stabilized cable ties provide excellent resistance to high heat exposures. • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

Product Dimensions

Min. Tensile Strength	30.0lbs / 135.0N
Length (L)	7.8 / 198.0mm
Width (W) (imperial)	0.14"
Width (W)	3.6mm
Min. Ø Bundle	1.5mm
Max. Ø Bundle	50.0mm

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
CSA Certified	No
Flammability	UL94 V2
Material Specification	HF
Operating Temperature	-40 °F to +257 °F (-40 °C to +125 °C)
ROHS Conformity	 RoHS
Specification	UL ZODZ2.E64139
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	1000
Carton Qty.	5000
UPC	089306272540

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512