


6GK1901-1BB10-2AE0 IE FC RJ45 PLUG 180 2X2

Technical Data



IE FC RJ45 PLUG 180 2X2, RJ45
PLUG CONNECTOR (10/100MBIT/S)
WITH RUGGED METAL HOUSING
AND FC CONNECTING METHOD,
FOR IE FC CABLE 2X2 180 DGR
CABLE OUTLET 1 PACK = 50 PCS

Transfer rate

- 1 / for Industrial Ethernet
- 2 / for Industrial Ethernet

10 Mbit/s
100 Mbit/s

Interfaces

Number of electrical connections

- for Industrial Ethernet FC TP cables
- for network components and terminal equipment

4
1

Design of the electrical connection / FastConnect

Yes

Mechanical data

material / of the housing

metal

Design, dimensions and weight

Width

13.7 mm

Height

16 mm

Depth

55 mm

Net weight

35 g

Permitted ambient conditions

Ambient temperature

- during operating
- during storage
- during transport

-40...+70 °C
-40...+80 °C
-40...+80 °C

Relative humidity

- at 25 °C / without condensation / during operating / maximum

95 %

Protection class IP	IP20
Product properties, functions, components / general	
Product feature / [not supplied - silicon-free]	Yes
Composant produit	
• décharge de traction	Yes
Standards, specifications, approvals	
Verification of suitability	
• RoHS conformity	Yes
• UL-registration	Yes
letzte Änderung:	May 14, 2012