



Sample photo

Order symbol: CAB ABS 504020 T3B
Product nbr: 8183062
Description: Cabinet, ABS
Remarks: Locks on the long side

EAN: 6418074020437
El. number:
Finland: 3424374
Denmark: 8212019072
Italy: 7812060
Sweden: 2540051
Norway:

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:				Rating:
Length	Width	Height		
mm: 500	400	200		Ingress Protection (EN 60529): IP 65
inch: 19.7	15.7	7.9		Impact Resistance (EN 62262): IK 08
Materials:				Electrical insulation: Totally insulated
Material:	ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:	Smoked grey			Glow Wire Test (IEC 695-2-1) °C: 650
Gasket material:	EPDM			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:				Certificates:
Short term:	-40 ... 80 °C			Fimko
Continuous:	-40 ... 60 °C			Europe EN 62208: 2003
Short term:	-40 ... 175 °F			Gost R
Continuous:	-40 ... 140 °F			
Accessories:				
EKIV 54	Mounting plate			
EKIV 37	DIN-35 Mounting rail			
DS35370E1	DIN-35 Mounting rail			
EKIV 47	DIN-35 Mounting rail			
DS35470E1	DIN-35 Mounting rail			
FP A 54	Swing-out door/Front plate			
MB 12225 AL	Swing door set			
FP 54	Front plate			
FP 18X2-54	Front plate			
DRF 54	DIN rail frame set			

