



Path: [Home](#) > [Rack Index](#) > Shelves (Fixed) - Internal Mount - Two Pair of Panel Rails



click to enlarge




**Assembly
Instructions**

Fixed Shelf (Unvented)

- Attach to the sides of both pair of rack combination rails
- Requires no front rail mounting
- Front & rear lip folded for extra strength
- Weight load tested (RFVS2426BK1) to 350 pounds!
- Versatile design - can be used as shown (easy to install) or upside down (front & rear lip become equipment retainers)
- Heavy duty, 14 Ga. steel construction
- Sides folded up for easy hardware installation from above
- Sides are slotted for easy adjustment with most rail depth locations
- Rugged textured powder paint finish
- Includes all mounting hardware
- If used with our square hole rails you will need to order P/N **CPRSA** rail adaptor for each shelf ordered.
(below) to more information.

**• MOUNTS ON TWO PAIR OF
PANEL RAILS (FRONT & BACK)**



click to enlarge



Assembly
Instructions

Fixed Shelf (Vented)

- Attach to the sides of both pair of rack combination rails
- Requires no front rail mounting
- Provides a sturdy shelf without obstructing upward heat movement
- Front & rear lip folded for extra strength
- Weight load tested (RFVS2426BK1) to 350 pounds!
- Versatile design - can be used as shown (easy to install) or upside down (front & rear lip become equipment retainers)
- Heavy duty, 14 Ga. steel construction
- Sides folded up for easy hardware installation from above
- Sides are slotted for easy adjustment with most rail depth locations
- Rugged textured powder paint finish
- Includes all mounting hardware
- If used with our square hole rails you will need to order P/N **CPRSA** rail adaptor for each shelf ordered.

(below) to more information.

- **MOUNTS ON TWO PAIR OF PANEL RAILS (FRONT & BACK)**

VENTED - 19" Rack Mount

Part Number	Color		Drawing File Size		.zip File Size	Shelf Depth
RFVS1918BK1	Black		61K		92K	18"
RFVS1918CG1	Grey/Beige					
RFVS1921BK1	Black		61K		94K	21"
RFVS1921CG1	Grey/Beige					

RFVS1926BK1	Black		65K		102K	26"
RFVS1926CG1	Grey/Beige					
RFVS1931BK1	Black		66K		103K	31"
RFVS1931CG1	Grey/Beige					



VENTED - 24 " Rack Mount

Part Number	Color		Drawing File Size		.zip File Size	Shelf Depth
RFVS2418BK1	Black		45K		76K	18"
RFVS2418CG1	Grey/Beige					
RFVS2421BK1	Black		47K		78K	21"
RFVS2421CG1	Grey/Beige					
RFVS2426BK1	Black		57K		97K	26"
RFVS2426CG1	Grey/Beige					
RFVS2431BK1	Black		54K		99K	31"
RFVS2431CG1	Grey/Beige					

Note: Weight load tested (RFVS2426BK1) to 350 pounds.

NOTES

FINISH: TEXTURED POWDER PAINT "BK1" BLACK OR "CG1" GRAY (RAL 7032)
10-32 MOUNTING SCREWS AND SPACER SHIMS ARE SUPPLIED WITH THE SHELF



SIDE VIEW

THIS DRAWING IS PROPRIETARY INFORMATION
OF HAMMOND MFG.CO.LTD. NOT TO BE USED
WITHOUT EXPRESSED WRITTEN PERMISSION
OF HAMMOND MFG.CO.LTD.

△	N/A	CUSTOMER INFORMATION		02 03 21	RJG
Rev	ECN	Description	Date	By	○

RFVS1926/A1

Unless Otherwise Spec'd
Dimensions are in inches
Tolerances are:
.X ±.1
.XX ±.06
.XXX ±.020
.XXXX ±.0050
Holes ±.0050
Angles ±.5°

Drawn
Date
Chk
Mat'l

R. GODFREY
02 03 21

14 GA STEEL

HAMMOND MANUFACTURING CO. LTD

W Enclosure Group, Guelph, Ontario, Canada

CONTEMPORA II
FIXED VENTED SHELF-RFVS

Ref. No. XXX


Part#: RFVS1926 Dwg: RFVS1926/A1

Shelves - Dual Pair Rail Mount

FIXED SHELVES

- Heavy duty, 14 Ga. steel construction, folded edges on all four sides for extra strength
- The vented version provides a sturdy shelf without obstructing upward heat movement
- Weight load tested to 350 pounds
- Sides folded up for easy hardware installation from above the shelf
- Sides are slotted for easy adjustment with most rail depth locations
- Rugged textured powder paint finish
- If used with our square hole rails you will need to order P/N **CPRSA** rail adaptor for each shelf ordered
- **MOUNTS ON TWO PAIR OF MOUNTING RAILS (FRONT & BACK)**

Vented



Unvented



Part Number		Shelf Type	Shelf Depth
Black Textured	Beige Textured		
19" Width			
RFVS1918BK1	RFVS1918CG1	Vented	18"
RFVS1921BK1	RFVS1921CG1	Vented	21"
RFVS1926BK1	RFVS1926CG1	Vented	26"
RFVS1931BK1	RFVS1931CG1	Vented	31"
RFUS1918BK1	RFUS1918CG1	Unvented	18"
RFUS1921BK1	RFUS1921CG1	Unvented	21"
RFUS1926BK1	RFUS1926CG1	Unvented	26"
RFUS1931BK1	RFUS1931CG1	Unvented	31"
24" Width			
RFVS2418BK1	RFVS2418CG1	Vented	18"
RFVS2421BK1	RFVS2421CG1	Vented	21"
RFVS2426BK1	RFVS2426CG1	Vented	26"
RFVS2431BK1	RFVS2431CG1	Vented	31"
RFUS2418BK1	RFUS2418CG1	Unvented	18"
RFUS2421BK1	RFUS2421CG1	Unvented	21"
RFUS2426BK1	RFUS2426CG1	Unvented	26"
RFUS2431BK1	RFUS2431CG1	Unvented	31"


SLIDING SHELVES

- Heavy duty, 14 Ga. steel construction, folded edges on all four sides for extra strength
- The vented version provides a sturdy shelf without obstructing upward heat movement
- Weight load tested to 120 pounds
- Slides are slotted for easy adjustment with most rail depth locations
- Rugged textured powder paint finish

Vented



Unvented



Part Number		Shelf Type	Shelf Depth
Black Textured	Beige Textured		
19" Width			
RSVS1918BK1	RSVS1918CG1	Vented	18"
RSVS1921BK1	RSVS1921CG1	Vented	21"
RSVS1926BK1	RSVS1926CG1	Vented	26"
RSVS1931BK1	RSVS1931CG1	Vented	31"
RSUS1918BK1	RSUS1918CG1	Unvented	18"
RSUS1921BK1	RSUS1921CG1	Unvented	21"
RSUS1926BK1	RSUS1926CG1	Unvented	26"
RSUS1931BK1	RSUS1931CG1	Unvented	31"
24" Width			
RSVS2418BK1	RSVS2418CG1	Vented	18"
RSVS2421BK1	RSVS2421CG1	Vented	21"
RSVS2426BK1	RSVS2426CG1	Vented	26"
RSVS2431BK1	RSVS2431CG1	Vented	31"
RSUS2418BK1	RSUS2418CG1	Unvented	18"
RSUS2421BK1	RSUS2421CG1	Unvented	21"
RSUS2426BK1	RSUS2426CG1	Unvented	26"
RSUS2431BK1	RSUS2431CG1	Unvented	31"

Accessories