

L754 MINIATURE CERAMIC FUSE LINKS

These size 00 (15.9mm x 4.7mm), sand filled fuse links have a high rupturing capacity and a category duty of 250V a.c. or 250V d.c. (Maximum prospective overload 4000A at 0.4pf and 250Va.c. and 230 V d.c. Time constant 0.004s.)

MINIMUM LIFE:

1,000 hours at rated current at temperatures up to 35°C. 1,000 hours continuous at 80% of rated current at temperatures beyond 35°C to 85°C.

TEMPERATURE RANGE:

-60°C to +85°C

MARKING:



Body marked with rating and approved versions carry the Joint Services' reference number

WEIGHT:

0.85g

ORDERING REFERENCE: L754/CURRENT RATING IN AMPERES

AVAILABLE IN : 50mA, 100mA, *250mA, *500mA, *1A, *2A
* Qualification Approved



BLP reserve the right to change without prior notice the information contained within this leaflet

BLP Components Ltd., Exning Road, Newmarket, Suffolk, CB8 0AX, England
Tel: +44 (0)1638 665161 Fax: +44 (0)1638 660718 email: sales@blpcomp.com <http://www.blpcomp.com>