




THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS 変更				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	E3	OBSOLETE 2--1	ECR-07-023693	31OCT07	AY	HY



- ① TO BE MEASURED WITHIN 2mm FROM **-Z-**
2. APPLICABLE P.C. BOARD THICKNESS: 1.6mm
3. THE MATING COUNTERPART PART NUMBER: 174045
4. RECOMMENDED MOUNTING SCREW: 3mm DIA, 6mm LENGTH TAPPING SCREW
SPECIFIED IN JIS B1115, B1122 (TIGHTENING TORQUE: 0.8N-M MAX.)
⑤ CIRCUIT NUMBER



- ① **-Z-**面より2mmの範囲で測定
2. 適用プリント基板厚: 1.6mm
3. 嵌合相手ハウジング型番: 174045
4. 推奨取付ネジ: JIS B1115, B1122 タッピンネジ, ナベ2種
呼び径3, 長さ6mm (締付けトルク0.8N-M以下)
⑤ 回路番号: 上図参照のこと

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差	
0 < x ≤ 10	±0.2
10 < x ≤ 30	±0.25
30 < x ≤ 100	±0.3
ANGLE ; 角度	±3°

PRE-TIN X 10		⑤ ⑥	黒 (BLACK)	4-174973-2
TIN-LEAD	SELECTIVE-GOLD X 2			
SELECTIVE-TIN	PRE-TIN	--	緑 (GREEN)	2-174973-4
SEE CUSTOMER DRAWING 2-174973-1				2-174973-1
PRE-TIN		--	緑 (GREEN)	174973-4
SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT)	--	黒 (BLACK)	174973-3
PRE-TIN		--	黒 (BLACK)	174973-2
TIN-LEAD	SELECTIVE-GOLD X 12	① ~ ⑫	黒 (BLACK)	174973-1
半田付け部 SOLDERING SIDE	接触部側 CONTACT SIDE	金めっき端子使用回路番号 CIRCUIT NO. OF GOLD PLATED CONTACT ⑤		色 COLOR
CONTACT 仕上げ FINISH OF CONTACT				型番 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 16APR02	Tyco Electronics AMP K.K. Kawasaki, Japan		
DIMENSIONS: 単位: 耗 MM		CHK A.YAMAGUCHI 16APR02			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD K.BETSUI 16APR02	NAME 名称 040 SERIES MULTI-LOCK I/O CONN. 12Pos CAP HOUSING ASSY (VERTICAL TYPE)		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 製品規格 108-5244	SIZE A3		
MATERIAL 材料 HOUSING: PBT CONTACT: BRASS		APPLICATION SPEC 取付適用規格	CAGE CODE 00779		
FINISH 仕上 SEE TABLE		WEIGHT 4.2 g	DRAWING NO 番号 C-174973		
		CUSTOMER DRAWING		SCALE 尺度 2:1	SHEET 1 OF 1
				REV E3	