

FLK 40/EZ-DR/ 300/SLC

Order No.: 2294652

The illustration shows version FLK 40/EZ-DR/200/SLC

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2294652>

Round cable sets, with 40-pos. socket strips in fixed lengths (50-cm steps) to connect to 32-channel I/O cards of the SLC 500, length 3 m

Commercial data

EAN	4017918149024
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.4366 KG
Catalog page information	Page 194 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
10/01/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 Ω /m

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Number of positions	40
Number of positions, control side	40
Number of connectors, control side	1
Number of positions, module side	40
Number of connectors, modul side	1
Fixed cable length	3 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
Test voltage	500 V AC (50 Hz, 1 min)
External diameter	10 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no
Standards/regulations	DIN EN 60352-4
	IEC 352-4

Certificates / Approvals



Certification

GOST

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;