


Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	2 STR/FLEX
Wire Type	Stranded Copper: Class B & C Compact, Class G, H, I, K, M, Locomotive
Wire Strip Length	1-7/16 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P33
Alternate Industry Die Index No. () on Barrel	(10)



Technical drawing of a Panduit LCBX2-38F cable jacket cross-section. The drawing shows a rectangular cross-section with a circular hole in the center. The hole is labeled "2 STR/FLEX LCBX2-38F". The outer dimensions are $.70 \pm .04$ (height) and $.36 \pm .04$ (width). The inner diameter of the hole is $.41 \pm .02$ DIA. The text "PANDUIT" is on the left, and "Wire inspection window" is on the right.



00	6/03	SAC		RELEASED	10850
REV	DATE	BY	CHK	DESCRIPTION	ECN

SCALE N/A	DRAWING NO / CAD FILE LCBX2-38F-CUST
--------------	---