


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1272	D	Elect. file renamed	JWM	12/19/01	DJC	12/27/01	DJC	12/27/01
1865	E	RoHS ADDED	DCM	10/18/05	JWM	10/19/05	JWM	10/19/05



NOTES:

1. Hold Diameter "A": 1/2" [12.7mm]
2. MATERIAL: NYLON 6/6
3. COLOR: NATURAL °F(75°C)
4. FLAMMABILITY RATING: UL94V-2
5. CONTINUOUS USE TEMPERATURE: -40°F(-40°C) TO 167
6. FRACTIONAL TOLERANCE = 1/64

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
 HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
 BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
 CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
 USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
 FOR THE INTENDED USE AND ASSUME ALL RISK AND
 LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
 Tolerances: Unless
 Otherwise Specified:
 .XX = ±.010
 .XXX = ±.005
 Fractional = ±1/64
 Angles = ±1°

DRAWN BY: C.M.D. DATE: 3/16/97
 CHECKED BY: D.D. DATE: 3/16/97
 APPROVED BY: D.D. DATE: 3/16/97

DRAWING TITLE: WIRE HARNESS CLIP
 SIZE DWG. NO. ELECTRONIC FILE REV
 A EHC-8 37N2119.dwg E
 SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1