

BRADY B-907 BRASS VALVE TAG

TDS No. B-907

Effective Date: 09/11/2023

Description: Brady B-907 valve tags are 260 grade, ½ hard temper brass.



Use:

Brady B-907 Brass Tags are used for general purpose valve identification.

Substrate Type:

Brass

Standard Legend Colors:

Natural or Black Fill

Thickness (PSTC-33):

Total: 0.032 in. (0.83 mm)

Service Temperature:

-40°F to 1200°F (-40°C to 649°C)

(Max. Ink Temp 180°F only.)

Average Outdoor Durability:

5-7 years (Average expected outdoor life of product will depend on user definition of failure and climatic conditions)

Chemical Resistance:

B907 with Natural Fill

REAGENT	7 DAY IMMERSION	DIP TEST	RUB TEST
30% Sulfuric Acid	NE	NE	NE
10% Sulfuric Acid	NE	NE	NE
30% Hydrochloric Acid	NE	NE	NE
10% Hydrochloric Acid	NE	NE	NE
Glacial Acetic Acid	NE	NE	NE
5% Acetic Acid	NE	NE	NE
50% Sodium Hydroxide	NE	NE	NE
10% Sodium Hydroxide	NE	NE	NE
10% Ammonia	F	NE	NE
5% Sodium Hypochlorite	NE	NE	NE
Methyl Ethyl Ketone	NE	NE	NE
Acetone	NE	NE	NE
Toluene	NE	NE	NE
1,1,1-Trichloroethane	NE	NE	NE
Methanol	NE	NE	NE
Isopropyl Alcohol	NE	NE	NE
Heptane	NE	NE	NE
Mineral Spirits	NE	NE	NE
Turpentine	NE	NE	NE
Kerosene	NE	NE	NE
Diesel Fuel	NE	NE	NE
Gasoline	NE	NE	NE
ASTM #3 Oil	NE	NE	NE

SAE 20 Oil	NE	NE	NE
10% Sodium Chloride	NE	NE	NE
Alconox®	NE	NE	NE
Water	NE	NE	NE

NE = No Effect

F = Failed (affected Sample)

7 Day Immersion: Immersed in reagent for 7 days.

Dip Test: Five 10 minute dips in reagent with 30-minute recovery.

Rub Test: Rubbed sample for 1 minute with swab soaked in reagent.

B-907 with Black Fill

REAGENT	7 DAY IMMERSION	DIP TEST	RUB TEST
30% Sulfuric Acid	NE	NE	NE
10% Sulfuric Acid	NE	NE	NE
30% Hydrochloric Acid	NE	NE	NE
10% Hydrochloric Acid	NE	NE	NE
Glacial Acetic Acid	F	F	NE
5% Acetic Acid	NE	NE	NE
50% Sodium Hydroxide	NE	NE	NE
10% Sodium Hydroxide	NE	NE	NE
10% Ammonia	F	NE	NE
5% Sodium Hypochlorite	NE	NE	NE
Methyl Ethyl Ketone	F	F	F
Acetone	F	F	F
Toluene	F	F	F
1,1,1-Trichloroethane	F	F	NE
Methanol	NE	NE	NE
Isopropyl Alcohol	NE	NE	NE
Heptane	NE	NE	NE
Mineral Spirits	NE	NE	NE
Turpentine	NE	NE	NE
Kerosene	NE	NE	NE
Diesel Fuel	NE	NE	NE
Gasoline	NE	NE	NE
ASTM #3 Oil	NE	NE	NE
SAE 20 Oil	NE	NE	NE
10% Sodium Chloride	NE	NE	NE
Alconox®	NE	NE	NE
Water	NE	NE	NE

NE = No Effect

F = Failed (affected Sample)

7 Day Immersion: Immersed in reagent for 7 days.

Dip Test: Five 10 minute dips in reagent with 30 minute recovery.

Rub Test: Rubbed sample for 1 minute with swab soaked in reagent.

Shelf Life:

Shelf Life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80°F (27°C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual application.

Trademarks:

Alconox® is a registered trademark of Alconox Co.

ASTM: American Society for Testing and Materials (U.S.A.)

SAE: Society of Automotive Engineers (U.S.A.)

PSTC: Pressure Sensitive Tape Council (U.S.A.)

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady

customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2020 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289