

6SE315

DRAWING	NUMBER
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
20	20
21	21
22	22
23	23
24	24
25	25
26	26
27	27
28	28
29	29
30	30
31	31
32	32
33	33
34	34
35	35
36	36
37	37
38	38
39	39
40	40
41	41
42	42
43	43
44	44
45	45
46	46
47	47
48	48
49	49
50	50
51	51
52	52
53	53
54	54
55	55
56	56
57	57
58	58
59	59
60	60
61	61
62	62
63	63
64	64
65	65
66	66
67	67
68	68
69	69
70	70
71	71
72	72
73	73
74	74
75	75
76	76
77	77
78	78
79	79
80	80
81	81
82	82
83	83
84	84
85	85
86	86
87	87
88	88
89	89
90	90
91	91
92	92
93	93
94	94
95	95
96	96
97	97
98	98
99	99
100	100

PAGE 1 OF 1

REPLACES

RELEASE NO. SR 11197

CHECK

৩৩

14, 1

五二

ACK

39

A 3

3


H

33

Aug



Σ

CORROSION RESISTANT
TREATED METAL ENCLOSURE



CORROSION RESISTANT
STEEL PLUNGER —————

ELASTOMER PLUNGER SEAL



(2) NO. 20 GAGE WIRE PER MIL-W-22759/9
EMBEDDED IN EPOXY CASTING RESIN

NOTE -

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS
- ② ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- ③ WEIGHT OF SWITCH ONLY IS .26 OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS .45 OZ MAX
- ④ WIRE LEADS MARKED WITH CIRCUIT IDENTIFICATION AND WIRE GAGE (CLOSED - 20 AND COMMON-20) PER MIL-W-5088

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	
OPERATING FORCE — — — — 5-17 OZ		CONTACT ARRANGEMENT S P N C		DO NOT SCALE PRINT	
RELEASE FORCE — — — — 4 OZ MIN		250 VAC — — — — — — — — — — 5 AMP		UNLESS OTHERWISE NOTED	
RELEASE TRAVEL — — — — .004 MIN		30 VOLTS DC RATING		DIMENSIONS ARE IN INCHES	
DIFFERENTIAL TRAVEL — — — .004 MAX		INDUCTIVE — — — — SEA LEVEL — — — 3 AMP		TOLERANCES ARE:	
OVERTRAVEL — — — — .003 MIN		50,000 FT — — — 2.5 AMP		ONE PLACE (.0) ±.030	
		RESISTIVE — — — — SEA LEVEL — — — 5 AMP		TWO PLACE (.00) ±.015	
		50,000 FT — — — 5 AMP		THREE PLACE (.000) ±.005	
		MAXIMUM INRUSH — — — — — — — — 24 AMP		ANGLES ±	
				WEIGHT 	

FORMTEK

DRAWN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[6SE315](#)