






Amp	Volt	Hz	IP Ident. colour + h	Part No.	Wall mount appliance inlets	2 P +  IEC/EN 60 309	 	EAN No. 4015609...																																	
					external fixing means, 1 top cable entry	  <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>Pg</th></tr><tr><td>16 A</td><td>45,5</td><td>5,3</td><td>74</td><td>60</td><td>60</td><td>28</td><td>110</td><td>13,5</td></tr><tr><td>32 A</td><td>60</td><td>5,3</td><td>97</td><td>82</td><td>80</td><td>45</td><td>141</td><td>21</td></tr></table>	Ampère	b	c	d	e	f	l	n	Pg	16 A	45,5	5,3	74	60	60	28	110	13,5	32 A	60	5,3	97	82	80	45	141	21	10 126 10 219	023066 023042 023097 023998 023981 024001						
Ampère	b	c	d	e	f	l	n	Pg																																	
16 A	45,5	5,3	74	60	60	28	110	13,5																																	
32 A	60	5,3	97	82	80	45	141	21																																	
16	230 110 400	50/60 50/60 50/60	6 4 9	610 306 610 304 610 309																																					
32	230 110 400	50/60 50/60 50/60	6 4 9	630 306 630 304 630 309																																					
					internal fixing means, 2 cable entries both, top and bottom (knock-out)	  <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>v</th><th>Pg</th></tr><tr><td>32 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>140</td><td>47,5</td><td>160</td><td>7</td><td>16/21</td></tr></table>	Ampère	b	c	d	e	f	l	n	v	Pg	32 A	66,5	5	96	95	140	47,5	160	7	16/21	5 349	024605 165902 165896													
Ampère	b	c	d	e	f	l	n	v	Pg																																
32 A	66,5	5	96	95	140	47,5	160	7	16/21																																
16	230 110 400	50/60 50/60 50/60	6 4 9	618 306 618 304 618 309																																					
cable gland Pg 16 enclosed																																									
32	230 110 400	50/60 50/60 50/60	6 4 9	638 306 638 304 638 309																																					
cable gland Pg 21 enclosed																																									
					internal fixing means, 2 cable entries both, top and bottom (knock-out)	  <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>u</th><th>v</th><th>Pg</th></tr><tr><td>16 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>140</td><td>47,5</td><td>154</td><td>72</td><td>7</td><td>16/21</td></tr><tr><td>32 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>147</td><td>47,5</td><td>164</td><td>96</td><td>7</td><td>16/21</td></tr></table>	Ampère	b	c	d	e	f	l	n	u	v	Pg	16 A	66,5	5	96	95	140	47,5	154	72	7	16/21	32 A	66,5	5	96	95	147	47,5	164	96	7	16/21	5 357 5 421	023820 023813 023837 024643 024636 024650
Ampère	b	c	d	e	f	l	n	u	v	Pg																															
16 A	66,5	5	96	95	140	47,5	154	72	7	16/21																															
32 A	66,5	5	96	95	147	47,5	164	96	7	16/21																															
63	230 110 400	50/60 50/60 50/60	6 4 9	668 306 668 304 668 309																																					
see page 2/141					external fixing means, 1 top cable entry	  <table><tr><th>Ampère</th><th>a</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>n</th><th>u</th><th>Pg</th></tr><tr><td>63 A</td><td>136</td><td>104</td><td>6</td><td>170</td><td>118</td><td>171</td><td>250</td><td>113</td><td>29</td></tr></table>	Ampère	a	b	c	d	e	f	n	u	Pg	63 A	136	104	6	170	118	171	250	113	29	2 825	024896 024889 024902													
Ampère	a	b	c	d	e	f	n	u	Pg																																
63 A	136	104	6	170	118	171	250	113	29																																
125																																									