



Product: [10GX62F](#) 

10GX Category 6A Enhanced Cable, 4 Bonded-Pairs, F/UTP, CMR

Product Description

10GX Category 6A Enhanced Premise Horizontal Cable (625MHz), 4 Bonded-Pairs, 23 AWG Solid Bare Copper Conductors, F/UTP - Foil Shielded, Riser-CMR, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet up to 10GBASE-T, Wi-Fi 6, Wi-Fi 5, Surveillance, HDBaseT, PoE++, PoE+, PoE, Noisy Environments
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/resources/patents .

Construction Details

Conductor

AWG	Stranding	Material	Number of Pairs
23	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown
Bonded-Pair:	Yes

Inner Jacket Material

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.26 in	Yes

Outer Shield Material

Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	26 AWG (7x34) TC

Outer Jacket Material

Separator Material	Material	Nom. Diameter	Ripcord
Center Member (Patented X-Spline®)	PVC - Polyvinyl Chloride	0.300 in	Yes

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. DCR Unbalanced Between Pairs [%]	Max. Capacitance Unbalance	Nom. Mutual Capacitance	Nom. Velocity of Prop.
82 Ohm/km	3%	5%	90 pF/100m	17 pF/ft	64%

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nom. Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	64%

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. PSANEXT	Min. PSAACRF	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	73.3 dB	71.2 dB	70.8 dB	68.8 dB	20.0 dB	100 ± 15 Ohm	105 ± 10 Ohm	77.0 dB	77.0 dB	40.0 dB	35.0 dB

4 MHz	3.8 dB/100m	64.3 dB	60.5 dB	58.8 dB	56.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	76.2 dB	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	59.8 dB	54.4 dB	52.7 dB	50.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	70.1 dB	40.0 dB	16.9 dB
10 MHz	5.9 dB/100m	58.3 dB	52.4 dB	50.8 dB	48.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	68.2 dB	40.0 dB	15.0 dB
16 MHz	7.5 dB/100m	55.2 dB	47.8 dB	46.7 dB	44.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	64.1 dB	38.0 dB	10.9 dB
20 MHz	8.4 dB/100m	53.8 dB	45.4 dB	44.8 dB	42.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	62.2 dB	37.0 dB	9.0 dB
25 MHz	9.4 dB/100m	52.3 dB	43.0 dB	42.8 dB	40.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	60.2 dB	36.0 dB	7.0 dB
31.25 MHz	10.5 dB/100m	50.9 dB	40.4 dB	40.9 dB	38.9 dB	25.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	77.0 dB	58.3 dB	35.1 dB	
62.5 MHz	15.0 dB/100m	46.4 dB	31.4 dB	34.9 dB	32.9 dB	25.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	77.0 dB	52.3 dB	32.0 dB	
100 MHz	19.1 dB/100m	43.3 dB	24.2 dB	30.8 dB	28.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	72.5 dB	48.2 dB	30.0 dB	
200 MHz	27.6 dB/100m	38.8 dB	11.2 dB	24.8 dB	22.8 dB	18.0 dB	100 ± 22 Ohm	100 ± 10 Ohm	68.5 dB	42.2 dB	27.0 dB	
250 MHz	31.1 dB/100m	37.3 dB	6.3 dB	22.8 dB	20.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	66.5 dB	40.2 dB	26.0 dB	
300 MHz	34.3 dB/100m	36.1 dB	1.9 dB	21.3 dB	19.3 dB	16.8 dB	100 ± 32 Ohm	100 ± 10 Ohm	65.3 dB	38.7 dB	25.2 dB	
350 MHz	37.2 dB/100m	35.1 dB	-2.1 dB	19.9 dB	17.9 dB	16.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	64.3 dB	37.3 dB	24.6 dB	
400 MHz	40.1 dB/100m	34.3 dB		18.8 dB	16.8 dB	15.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	63.5 dB	36.2 dB	24.0 dB	
450 MHz	42.7 dB/100m	33.5 dB		17.7 dB	15.7 dB	15.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	62.7 dB	35.1 dB	23.5 dB	
500 MHz	45.3 dB/100m	32.8 dB		16.8 dB	14.8 dB	15.2 dB	100 ± 32 Ohm	100 ± 10 Ohm	62.0 dB	34.2 dB	23.0 dB	
550 MHz	47.7 dB/100m	32.2 dB		14.9 dB	14.0 dB	14.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	62.4 dB	34.4 dB		
600 MHz	50.1 dB/100m	31.6 dB			13.2 dB	14.7 dB	100 ± 32 Ohm	100 ± 10 Ohm	61.8 dB	33.6 dB		
625 MHz	51.2 dB/100m	31.4 dB			12.9 dB	14.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	61.6 dB	33.3 dB		
750 MHz	56.7 dB/100m	30.2 dB			11.3 dB	14.0 dB	100 ± 32 Ohm	100 ± 10 Ohm	60.4 dB	31.7 dB		
860 MHz	61.2 dB/100m	29.3 dB			10.1 dB	13.6 dB	100 ± 32 Ohm	100 ± 10 Ohm	59.5 dB	30.5 dB		

Voltage

UL Voltage Rating
300 V (CMR)

Mechanical Characteristics

Temperature

UL Rating	Operating	Installation	Storage
75°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.2 in	3.0 in

Max. Pull Tension:	40 lbs
Bulk Cable Weight:	39 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Riser, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Fire Resistance:	UL 1666 Riser, FT4, FT4, IEC 60332-1-2
NEC / UL Compliance:	800, CMR
CEC / C(UL) Compliance:	CMR
ICEA Compliance:	S-116-732-2013
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6A
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	Verified Channel/Category 6A

Part Number

Plenum Number:	10GX63F
----------------	---------

Variants

Item #	Color	Putup Type	Length	UPC
--------	-------	------------	--------	-----

10GX62F 0101000	Black	Reel	1,000 ft	612825102465
10GX62F 0061000	Blue	Reel	1,000 ft	612825102434
10GX62F 0081000	Gray	Reel	1,000 ft	612825102441
10GX62F 0021000	Red	Reel	1,000 ft	612825102410
10GX62F 0091000	White	Reel	1,000 ft	612825102458
10GX62F 0041000	Yellow	Reel	1,000 ft	612825102427

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 625 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	--

History

Update and Revision:	Revision Number: 0.412 Revision Date: 07-28-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.