

## HC-B 10-TFL-52/O1M25S

Order No.: 1604761



HEAVYCON sleeve housing B10, for single locking latch, height 52 mm, with support 1x M25, lateral conductor exit

### Commercial data

GTIN (EAN)	4 017918 882532
sales group	D002
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 570 (PC-2011)

### Product notes

WEEE/RoHS-compliant since:  
01/31/2006



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### General data

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24
Design	B10
Height	52 mm
Width	43 mm
Length	73 mm

Housing type	Sleeve housings
Locking type	for single locking latch
No. of cable exits	1
Cable exit	Lateral
Pg screw connection	None
Type of the screw connection	1x M25
Degree of protection for housing	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray

### Certificates / Approvals



Certification

GOST

### Diagrams/Drawings

Dimensioned drawing

