

TK-type Twin Wheel Caster




Characteristic

Caster with cover, drivability, stability, and smooth turning are excellent.

Application

Lighter devices / TV tables



caster with stopper
(applicable for
both truck and bolt types)

Bolt Type Specification

Model No.	A	D	E	d	H2	K	L	W	Allowable Load (kg)	Code No.					
TK30N6	29	φ30	11	M6×1.0	39	10	14	33	20	19034					
TK40N8	39.5	φ42	14	M8×1.25	55	14	15	39	30	19037					
TK40N8S	47			M10×1.5						19050					
TK40N10	39.5									19038					
TK40N10S	47			W5/16×-18						19051					
TK40N2.5	39.5									19039					
TK40N2.5S	47			W3/8×-16						19052					
TK40N3	39.5									19040					
TK40N3S	47									19053					
TK50N8	51.5			φ52						21	M8×1.25	65	19	15	46.5
TK50N8S	59	M10×1.5	19055												
TK50N10	51.5		M12×1.25		19043										
TK50N10S	59	19056													
TK50N12	51.5	W5/16×-18	65		19	15	46.5		19044						
TK50N12S	59								19057						
TK50N2.5	51.5	W3/8×-16			14				19045						
TK50N2.5S	59								19058						
TK50N3	51.5	19046													
TK50N3S	59	19059													

※N shows the screw type on the model No. Caster with stopper has S at the end of the model No.


Truck Type Specification

Model No.	A	D	E	G	H1	L1	L2	P1	P2	W	Allowable Load (kg)	Code No.
TK30	29	φ30	11	φ5	42.5	28	28	18	18	33	20	19031
TK40	39.5	φ42	14		58.5	38	38	26	26	40.5	30	19032
TK40S	47											19047
TK50	52.5	φ52	21		68.5					47	40	19033
TK50S	59											19048

※Caster with stopper has S at the end of the model No.

Model No.	Material	
	Body	Wheel
TK-Type	PA	PA

Bolt type



Truck type

