

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212010015](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form A-18mm, External Thread, 3 Pole Plus Ground Terminal, 250V AC/DC, Gray, Nitrile Gasket, Unmounted, Single Pack



Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-121201-C28-001 \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#) [Test Summary TS-121201-001-001 \(PDF\)](#)
[Product Specification STR-1251-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [121201](#)
Form A - 18mm
IP Rating IP65, IP67
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Type Field Attachable Connector
UPC 883906916169

Physical
Cable Diameter N/A
Coupling Type External Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polyamide
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 22.541/g
Orientation 90° Angle
Pitch - Mating Interface 18.00mm
Poles 3
Temperature Range - Operating -40°C to +90°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 16.0A
Voltage - Maximum 250V AC/DC

Material Info
Engineering Number C28300G0R

Reference - Drawing Numbers
[Packaging Specification](#) PK-121201-C28-001
[Product Specification](#) PS-121201-001-001, STR-1251-001
[Sales Drawing](#) SD-121201-003-001
[Test Summary](#) TS-121201-001-001

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
ED/71/2019 (16 July
2019)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[121201](#) Series