

TCP 40/DC32V

Order No.: 0700040

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=0700040>

Miniature circuit-breaker, Number of positions: 1, Nominal current: 40 A, Nominal voltage: 32 V, Width: 6 mm, Fuse type: Slow-blow, Fuse type: Automatic device, Mounting type: Base assembly (pluggable), Color: orange

Commercial data

EAN	4046356079891
Pack	50 pcs.
Customs tariff	85362010
Weight/Piece	0.005 KG

Product notes

WEEE/RoHS-compliant since:
06/21/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Color	orange
Insulating material	PA
Inflammability class acc. to UL 94	V0

Dimensions

Width	6 mm
Length	20 mm

Technical data

Fuse	Slow-blow
Fuse type	Automatic device
Nominal current I_N	40 A
Nominal voltage U_N	32 V AC/DC
Switching capacity I_{CN}	(150 A for nominal currents 5A to 30 A)
Ambient temperature (operation)	-30 °C ... 60 °C

Additional products

Item	Designation	Description
General		
3036372	ST 4-FSI/C	Fuse terminal block with LED for mounting on NS 35, for miniature circuit breakers, terminal width: 8.2 mm, color: Black
3036495	ST 4-FSI/C-LED 12	Fuse terminal block with LED for mounting on NS 35, for miniature circuit breakers, terminal width: 8.2 mm, color: Black
3036505	ST 4-FSI/C-LED 24	Fuse terminal block with LED for mounting on NS 35, for miniature circuit breakers, terminal width: 8.2 mm, color: Black
3118203	UK 6-FSI/C	Flat-type fuse terminal block, cross section: 0.2 - 6 mm ² , AWG: 26 - 8, width: 8.2 mm, color: black
3001925	UK 6-FSI/C-LED12	Flat-type fuse terminal block, cross section: 0.2 - 6 mm ² , AWG: 26 - 8, width: 8.2 mm, color: black, with light indicator, voltage light indicator: 12 V DC, current light indicator: 2 mA
3001938	UK 6-FSI/C-LED24	Flat-type fuse terminal block, cross section: 0.2 - 6 mm ² , AWG: 26 - 8, width: 8.2 mm, color: black, with light indicator, voltage light indicator: 24 V DC, current light indicator: 2 mA

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;