



MH433

433 MHz 1/4 Wave
Helical Antenna

Features

- ◆ Moulded Helical Antenna
- ◆ External Mount
- ◆ SMA-Male connector
- ◆ Ideal for ISM-Band applications

Specifications

Specifications	
Frequency	433 MHz
Polarisation	Linear
Return Loss	- 23 dB
Bandwidth	8% @ centre frequency
Power Rating	50W
Cable / Connector	SMA-Male
Dimensions	75x12.5mm

Ordering Options

Ordering Options	
FMH35076-SM-ST	MH433 with SMA-Male Connector


Specifications subject to change without notice.

5 Little Balmer
Buckingham Industrial Park
Buckingham
MK18 1TF
UK


Tel: +44 (0)1280 824055
Fax: +44 (0)1280 817179
Email: sales@ead-ltd.com
Web: www.ead-ltd.com

MH433 | 433 MHz 1/4 Wave Helical Antenna

Return Loss



Outline Drawing



Specifications subject to change without notice.

5 Little Balmer
Buckingham Industrial Park
Buckingham
MK18 1TF
UK

Tel: +44 (0)1280 824055
Fax: +44 (0)1280 817179
Email: sales@ead-ltd.com
Web: www.ead-ltd.com

EAD
embedded antenna design ltd
Delivering Antenna Innovation