

Receptacle Contacts (continued)

Standard Receptacle Contacts with Modified Spring

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers					Hand Tool 539635-1 with Die Set
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *	
0.2–0.5	–	1.15–1.60	-1	964322	2,300	964321	500	x-878712-x	539665-2
0.5–1.0	–	1.4–2.1	-1	964324	2,300	964323	500	x-878713-x	
> 1.0–2.5	–	2.2–3.0	-1	964326	2,300	964325	500	x-878714-x	
> 2.5–4.0	–	3.3–4.5	-1 / -5	964328	2,100	964327	500	x-878711-x	

Receptacle Contacts with Modified Spring and Single Wire Sealing System

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers					Hand Tool 539635-1 with Die Set
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *	
0.5–1.0	–	1.4–2.7	1-xxx-1 / 1-xxx-2	964330	1,700	964329	500	x-878337-x	539666-2
0.5–1.0	1.4–2.7	–	-1	969040	1,500	969041	500	x-541566-x	
> 1.0–2.5	–	2.2–3.7	-5 / 1-xxx-1 / 1-xxx-2	964332	1,700	964331	500	x-878338-x	
> 1.0–2.5	2.2–3.7	–	-1	969042	1,500	969043	500	x-541567-x	
> 2.5–4.0	3.4–4.5	3.4–4.5	1-xxx-1	964334	1,500	964333	500	x-878719-x	
> 2.5–4.0	3.4–4.5	3.4–4.5	-1 / -5	969044	1,500	969045	500	x-541568-x	

*) **Material and Finish:**
xxx-1 = CuFe, pre-tin plated
xxx-5 = CuFe, pre-silver plated
1-xxx-1 = CuFe, pre-tin plated
1-xxx-2 = CuFe, selective gold plated

*) The pre- and suffix for the applicators depends on the applied termination equipment.