

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [03-06-2361](#)
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter Standard .062" Pin and Socket Plug Housing, 36 Circuits, 4 Rows, with Mounting Ears

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [1772](#)
Application Power, Wire-to-Wire
Comments Dimensions B and D are based on a pitch of 4.19mm.
The drawing below shows a pitch of 3.68mm.
MolexKits Yes
Overview [Standard .062" Pin and Socket Power Connectors](#)
Product Name Standard .062"
UPC 800753615328

Physical

Circuits (maximum) 36
Flammability 94V-2
Gender Dual
Glow-Wire Compliant No
Lock to Mating Part Yes
Net Weight 7.440/g
Number of Rows 4
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 4.20mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Electrical


Current - Maximum per Contact 4A

Material Info

Old Part Number 1772-36P

Reference - Drawing Numbers

Sales Drawing SD-1772-36*-*-*



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[1772Series](#)

Mates With
[03-06-1362](#)

Use With
Male Crimp Terminals [1560](#) , [1786](#) , [1854](#) .
[1778](#) . Female Crimp Terminals [1561](#) , [4559](#) ,
[4529](#) , [2190](#) , [2189](#) , [1787](#) , [1855](#) , [1779](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

03-06-2361