







Circuits	Dimension	
	A	B
4	8.45	2.54
6	10.99	5.08
8	13.53	7.62
10	16.07	10.16
12	18.61	12.70
14	21.15	15.24
16	23.69	17.78
18	26.23	20.32
20	28.77	22.86
22	31.31	25.40
24	33.85	27.94
26	36.39	30.48

Specifications:
Current rating:1.5A AC,DC
Voltage rating:230V AC, DC
Contact resistance:20m ohm Max
Insulation resistance:1000M ohm Min
Withstanding voltage:AC 500V AC/minute
Operating Temperature:-40°C ~ +105°C
Materials and Finish
Insulator:PBT (UL94V-0)
Contact material:Phosphor Bronze
Finish:Tin Plated

How to Order



PCB Layout



TOLERANCE (mm)	APPROVALS	DATE	TITLE		AMPHENOL	
X. ±0.3	DRAWN Stephane	2009/10/07	TMM Series IDC Transition Plug		Amphenol European Design Center	
X.X ±0.2	CHECKED Rob	2009/10/07			Scale N.A. Sheet 1 of 1	
X.XX ±0.15	APPROVED Rob	2009/10/07				
UNLESS OTHERWISE SPECIFIED			UNIT :	SIZE : A4	DRAWING N° TMM-2-0-XX-X	
						REV. E