


DC Power Jack

163-2217

KOBI CONN

DC Power Jack



DIMENSIONS: mm (IN)

SPECIFICATIONS	
Voltage Rating:	12VDC
Current Rating:	1A
Contact Resistance:	30m Ω
Insulation Resistance:	100m Ω 500VDC
Dielectric Strength:	500VAC 1 min.
Durability:	5000 cycles
Insertion Force:	.2Kg to 2.0Kg
Extraction Force:	.2Kg to 2.0Kg
Soldering Temperature:	260° for 5 seconds
Operating Temperature:	-25°C to +85°C
Material Contacts:	Brass
Material Housing:	PBTG15% Black
Plating:	Tin

Date Last Revised: 10-14-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300400

163-2217

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[163-2217](#)