



MMS-108-01-L-SV

MMS-116-02-L-DV

MMS SERIES

TIGER CLAW™ SOCKET STRIP

UL[®]
FILE NO. E111594



FILE NO. E111594

FILE NO: 090871 0 05

MMS	1	NO. PINS PER ROW	01	PLATING OPTION	ROW OPTION	OTHER OPTION
02 thru 40			-F = Gold flash on contact, Matte Tin on tail -L = 10μ" ($0,25\ \mu\text{m}$) Gold contact, Matte Tin on tail	-SV = Single Vertical -SH = Single Horizontal -DV = Double Vertical -DH = Double Horizontal	-“XX” = Polarized Position	
No. of positions x $(2,00) .0787 + (0,56) .022$			-SV	-SH	-DV	-DH

MMS	1	NO. PINS PER ROW	02	PLATING OPTION	ROW OPTION	OTHER OPTION
02 thru 40				-F = Gold flash on contact, Matte Tin on tail	-SV = Single Vertical	-“XX” = Polarized Position
				-L = 10μ" (0,25 μm) Gold contact, Matte Tin on tail	-SH = Single Horizontal	-K = (5,50 mm) .217" DIA Polyimide Film Pick & Place Pad (-SV & -DV only) (-SV= 3 positions min.) (-DV= 4 positions min.)
				-S Row (3,81) .150 x (7,62) .300 -D Row (5,71) .225 x (10,01) .394	-DV = Double Vertical	-M = Metal Pick & Place Pad (4 positions min.) (-DV only)
					-DH = Double Horizontal	-P = Plastic Pick & Place Pad (4 pos. min., -SV only) (5 pos. min., -DV only)
						-TR = Tape & Reel Packaging

Due to technical progress, all designs, specifications and components are subject to change without notice.