



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm sliding sleeve system
 ▶ 4 mm safety system
sockets
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ plugs ▶ plugs ▶ VQ 20

VQ 20

datasheet for VQ 20
article number: 930058104



[View Full-Size Image](#)



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:		order number: 930 058-104	
description:		Fully mating connector, shatter-proof, flexible insulated sleeve with transverse hole. The tapering sleeve end also serves as kinking protection for the lead. Solder connection up to maximum cable cross-section of 1.5 mm². Nickel-plated brass contact material.	
typ:		VQ 20 gruen/green	
system:		4mm system	
order number:		930 058-104	
color			
other color versions:			
technical data			
measurement category acc. to IEC 61010:		CAT I	
pin dimensions		4 mm	
type of contact:		pin (spring loaded)	
type of termination:		screw	
rated voltage:		30 VAC / 60 VDC	
rated current:		16 A	
Please consider derating curve!			
contact resistance:		3 mOhm	
material			
contact material:		brass	
contact surface material:		nickel	
housing material:		PVC - P	
environmental conditions:			
temperature range:		-25 °C to +70 °C	
drawing			
			