



## SYDNEY fire proof safes

**Fire protection for home and office at a very low price.  
Feel confident in the security of your irreplaceable items.**

These modern designed safes are convenient and reliable in operation.

- Fire resistance – LFS 60 P according to EN 15659  
The safe was aflamed for one hour and the interior will remain below 170°C to protect your valuable and irreplaceable documents.
- The double walled construction is filled with a fire resistant concrete.
- Solid metal locking bolts help to prevent unwanted entry and access.
- Bolt down kit included to prevent unauthorized removal
- one tray for storage of easy-to-misplace-items
  - Model Sydney 40, 55 & 65 have the tray on the top
  - Model Sydney 140 has the tray on the bottom
- advanced jutting electronic key locking system powered by 4 1,5 V batteries (not included)
  - Model Sydney 40 & 55 are equipped with a turning handle
  - Model Sydney 65 & 140 are equipped with a hand lever
- special features of Model Sydney 65 & 140
  - panic function – door will be locked automatically in cause of closing
  - tray can be closed with a cylinder lock



pic.: Sydney 40



pic.: Sydney 140

Model	Art. No.	External Dim. mm H x W x D	Interior Dim. mm H x W x D	Clear Opening H x W	Weight kg	Vol. litre	shelf	Tray High mm
Sydney 40	T05436	320 x 445 x 450	210 x 340 x 290	172 x 340	38	21	0	40
Sydney 55	T05437	515 x 445 x 450	405 x 340 x 290	406 x 340	51	41	1	40
Sydney 65	T05438	715 x 485 x 475	525 x 345 x 300	439 x 345	86	54	2	87
Sydney 140	T05439	1390 x 710 x 625	1170 x 545 x 405	1030 x 545	310	258	3	140

Note: External high incl. socket, external depth incl. cover, Interior high and volume incl. tray

[www.rottner-tresor.com](http://www.rottner-tresor.com)

Updated: 30.01.2012