




RECOMMENDED
CABLE STRIPPING DIM'S



1. CRIMPED FERRULE
HEX CRIMP SIZE .305"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

REV.	DATE	ECR NO.	DESCRIPTION
A	11/20/97	XXXXXX	ADD CENTER CONTACT
B	07/19/07	XXXXXX	UPDATE DRAWING FORMAT
C	08/04/10	2084	ADD HEX CRIMP DEMENSIONS TO DRAWING

9	FERRULE	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex						
8	CONTACT PIN	BRASS	GOLD	1		DRAWN	M.ZHANG							08/04/10
7	WASHER	BRASS	NICKEL	1		CHECKED								
6	RING	DELTRIN	NATURAL	1		ISSUED			PART DESCRIPTION					
5	RETAINER RING	BRASS	NICKEL	1		SHEET	1 OF 1		TNC CRIMP PLUG – 75 OHM (FOR RG-6/U CABLE)					
4	GASKET	RUBBER	RED	1		PART NO.								
3	INSULATOR	DELTRIN	NATURAL	2		122390								
2	BODY	BRASS	NICKEL	1		DWG. NO.								
1	SHELL	BRASS	NICKEL	1		122390.DWG								
	DESCRIPTION	MATERIAL	FINISH	QTY		REV. C								
					SIZE A									
					SCALE NA									