

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

MARCH ,2006.

© COPYRIGHT 2006

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

E

B

B

ECR-07-012186

21/05/07

AM

FWK

NOTES:

1. ELECTRICAL DATA:

CONTACT RESISTANCE: 10 mOhm MAX

INSULATION RESISTANCE: 100 MOhm MIN at 500VDC

CURRENT RATING: 5 AMPS

BREAKDOWN VOLTAGE: 500 VAC MIN PER MINUTE

2. ENVIRONMENTAL:

OPERATING TEMPERATURE: -25°C TO +90°C

SEALING REQUIREMENTS: IP67

3. PROD SPEC:

108-3641

4. PACKAGING:

107-3334

5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE

6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

PIN ASSIGNMENTS

FRONT VIEW

2

1

5

3

4

SHIELD

DRAIN WIRE

5

GREEN

4

BLACK

3

BLUE

2

WHITE

1

BROWN

PIN

WIRE COLOUR

40.1

ø14.4

M12.0 x 1.0

2

1

5

6

7

3

tyco

'A'±'B'

4

ø5.0

10000

500 mm

M12 STRAIGHT MALE CONNECTOR 10.0m CABLE

1838370-5

7000

350 mm

M12 STRAIGHT MALE CONNECTOR 7.0m CABLE

1838370-4

5000

250 mm

M12 STRAIGHT MALE CONNECTOR 5.0m CABLE

1838370-3

3000

150 mm

M12 STRAIGHT MALE CONNECTOR 3.0m CABLE

1838370-2

2000

100 mm

M12 STRAIGHT MALE CONNECTOR 2.0m CABLE

1838370-1

DIM A

TOL 'B'

DESCRIPTION

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0

PLC

±

-

1

PLC

±

-

2

PLC

±

-

3

PLC

±

-

4

PLC

±

-

ANGLES

±

-

FINISH

±

-

DWN

MANJUNATH.T.N

03APR06

CHK

F.WHEELER-KING

07AUG06

APVD

F.WHEELER-KING

07AUG06

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

tyco

Electronics

Tyco Electronics Corporation

Bideford, UK, EX39 4HE

NAME

M12 SHIELDED, STRAIGHT MALE CONNECTOR WITHOUT STRAIN RELIEF 5 POSITION, PU CABLE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1838370

-

SCALE

NTS

SHEET

1

OF

1

REV

B

AMP 1470-19 REV 31MAR2000