

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

64320-2319

Status:

Active

Overview:

CMC and CMX Sealed, Hybrid, Modular Connectors

Description:

.635mm, 1.50mm, CMC Receptacle, 36 Circuits, Left Wire Output, Brown Coding, Mat Sealed, Row 1 Closed



Documents:	
3D Model	Application Specification AS-98420-002 (PDF)
Drawing (PDF)	Application Specification AS-98420-002-CH (PDF)
Application Specification AS-64319-002 (PDF)	Application Specification AS-98420-002-FR (PDF)
Application Specification AS-64319-002-CH (PDF)	Application Specification AS-98420-002-SP (PDF)
Application Specification AS-64319-002-FR (PDF)	Packaging Specification PK-64320-001 (PDF)
Application Specification AS-64319-002-SP (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	64320
Application	Power, Wire-to-Board
Application Tooling Part Link	63812-1100
Application Tooling Part Link	63824-1200
Comments	* Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C . Current max = 6.0A for 0.635mm Terminal (0.75mm² wire) and 12.0A for 1.50mm Terminal (2.00mm² wire) *
More Detailed Tech Information	Sealed, high-density, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC
UPC	883906131128

Physical	
Circuits (maximum)	36
Circuits Detail	6 x 1.5mm, 30 x 0.635mm terminals
Color - Resin	Brown
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	36.031/g
Number of Rows	3
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical	
Current - Maximum per Contact	12A, 6A

Material Info

Reference - Drawing Numbers

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

64320Series

Mates With

36638 CMC Header

Use With

CMC CP Female Terminal [64322](#) , [64323](#). Circuit Way Plugs, [64325-1010](#) , [64325-1023](#). CMC Wire Cap, [64320-1301](#). CMC 48 Circuit Header, [36638](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Continuity Test Pen Assembly	0638121100
Unlocking Tool for CMC and	0638241200

Application Specification

Packaging Specification
Sales Drawing

AS-64319-002, AS-64319-002-CH, AS-64319-002-FR,
AS-64319-002-SP, AS-98420-002, AS-98420-002-CH,
AS-98420-002-FR, AS-98420-002-SP
PK-64320-001
SD-64320-003

CMX Receptacle
Connector

This document was generated on 10/02/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION