






QVT

Split cable glands



Type	Order No.	Cable inserts	Thread Thread length	PU	Description
QVT 20	45695	1 x QT	M20 x 1.5 Length: 13 mm	10	
QVT 25	45702	1 x QT	M25 x 1.5 Length: 13 mm	10	
QVT 32	45711	1 x QT	M32 x 1.5 Length: 13 mm	10	
QVT 40 2	45715	2 x QT	M40 x 1.5 Length: 13 mm	10	
QVT 50 4	45722	4 x QT	M50 x 1.5 Length: 13 mm	10	

1

Product description

QVT is a circular split frame for quick and easy installation of cables or complete cable harnesses.

The QVT range is especially suitable for small machines, devices and instruments, because of the extremely small structure.

Advantages

- Compact and small structure
- Routing of assembled cables
- Warranty of pre-terminated cables remains
- Retrofitting and maintenance can be carried out easily and quickly
- Suitable for metric or standard hole sizes
- Locknut is part of delivery.

Specification

Material	Polycarbonate
Colour	similar RAL 7035
Flame class	UL-94 Vo, self-extinguishing
Protection class	IP 54, with gasket and correct selection of the cable inserts
Temperature	- 30°C to + 100°C (static)
Properties	halogen-free, silicone-free
Cut-out dimension	metric standard sizes

Accessories

QT Cable inserts	Page 41
KVT-EMC bracket	Page 93
KGM locknut	Page 124